

List Prices subject to change without notice
Visit our website for the most current information.



BRONZE Y-STRAINER — SOLDER END W/PLUG

Fig. No.	Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
S-221-A Class 125 20 Mesh Screen w/Plug	List Price	N/A	N/A	\$ 57.15	\$ 68.36	\$ 95.25	\$ 139.00	\$ 160.30	\$ 260.00	N/A	N/A
	Box Qty	—	—	10	5	5	2	2	2	—	—
	Unit Wgt.	—	—	.57	1.01	1.59	2.68	3.99	6.94	—	—
	Case Qty.	—	—	50	30	25	10	10	6	—	—
	UPC 039923-	—	—	279927	279934	279941	279958	279965	279972	—	—
S-222-A Class 125 Perforated Stainless Steel w/Plug	List Price	N/A	N/A	\$ 65.00	\$ 76.21	\$ 104.20	\$ 154.70	\$ 177.10	\$ 288.00	N/A	N/A
	Box Qty	—	—	10	5	5	2	2	2	—	—
	Unit Wgt.	—	—	.57	1.01	1.59	2.68	3.99	6.94	—	—
	Case Qty.	—	—	50	30	25	10	10	6	—	—
	UPC 039923-	—	—	280091	280107	280169	280176	280183	280190	—	—



BRONZE Y-STRAINER — SOLDER END W/SOLID CAP

Fig. No.	Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
S-221-B Class 125 20 Mesh Screen w/Solid Cap	List Price	N/A	N/A	\$ 57.15	\$ 68.36	\$ 96.37	\$ 137.90	\$ 159.10	\$ 257.80	N/A	N/A
	Box Qty	—	—	10	5	5	2	2	2	—	—
	Unit Wgt.	—	—	.57	1.01	1.59	2.68	3.99	6.94	—	—
	Case Qty.	—	—	50	30	25	10	10	6	—	—
	UPC 039923-	—	—	279989	279996	280008	280060	280077	280084	—	—
S-222-B Class 125 Perforated Stainless Steel w/Solid Cap	List Price	N/A	N/A	\$ 61.64	\$ 72.85	\$ 102.00	\$ 150.20	\$ 170.40	\$ 280.20	N/A	N/A
	Box Qty	—	—	10	5	5	2	2	2	—	—
	Unit Wgt.	—	—	.57	1.01	1.59	2.68	3.99	6.94	—	—
	Case Qty.	—	—	50	30	25	10	10	6	—	—
	UPC 039923-	—	—	280206	280213	280251	280268	280275	280282	—	—



BRONZE Y-STRAINER — THREADED END W/ PLUG

Fig. No.	Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
T-221-A Class 125 20 Mesh Screen w/Plug	List Price	\$ 54.91	\$ 54.91	\$ 54.91	\$ 75.09	\$ 96.37	\$ 134.60	\$ 161.40	\$ 277.90	\$ 607.00	\$ 828.00
	Box Qty	10	10	10	5	5	2	2	2	1	1
	Unit Wgt.	.74	.71	.81	1.13	1.85	2.96	4.47	7.45	14.94	21.96
	Case Qty.	50	50	50	30	25	10	10	6	3	2
	UPC 039923-	280299	280305	280312	280350	280367	280374	280381	280398	280442	280459
T-222-A Class 125 Perforated Stainless Steel w/Plug	List Price	\$ 57.15	\$ 57.15	\$ 57.15	\$ 80.68	\$ 103.10	\$ 145.80	\$ 171.50	\$ 297.00	\$ 650.00	\$ 887.00
	Box Qty	10	10	10	5	5	2	2	2	1	1
	Unit Wgt.	.74	.71	.81	1.13	1.85	2.96	4.47	7.45	14.94	21.68
	Case Qty.	50	50	50	30	25	10	10	6	3	2
	UPC 039923-	280619	280626	280633	280640	280657	280664	280671	280688	280695	280701

NIBCO[®]
AHEAD OF THE FLOW[®]

NIBCO INC.
WORLD HEADQUARTERS
WEB: www.nibco.com

1516 MIDDLEBURY STREET
ELKHART, IN 46516-4740
USA

DOMESTIC CUSTOMER SERVICE
PHONE: 800.234.0227
FAX: 800.234.0557

TECHNICAL SERVICE
PHONE: 888.446.4226
FAX: 888.336.4226

INTERNATIONAL OFFICE
PHONE: +1/574.295.3327
FAX: +1/574.295.3455



BRONZE Y-STRAINER — THREADED END W/SOLID CAP

Fig. No.	Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
T-221-B Class 125 20 Mesh Screen w/Solid Cap	List Price	\$ 52.67	\$ 52.67	\$ 52.67	\$ 72.85	\$ 95.25	\$ 133.40	\$ 159.10	\$ 274.60	\$ 601.00	\$ 821.00
	Box Qty	10	10	10	5	5	2	2	2	1	1
	Unit Wgt.	.74	.71	.81	1.13	1.85	2.96	4.47	7.45	14.94	21.68
	Case Qty.	50	50	50	30	25	10	10	6	3	2
	UPC 039923-	280466	280473	280480	280497	280541	280558	280565	280572	280596	280602
Fig. No.	Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
T-222-B Class 125 Perforated Stainless Steel w/Solid Cap	List Price	\$ 54.91	\$ 54.91	\$ 54.91	\$ 78.45	\$ 98.62	\$ 139.00	\$ 164.80	\$ 285.80	\$ 626.00	\$ 849.00
	Box Qty	10	10	10	5	5	2	2	2	1	1
	Unit Wgt.	.74	.71	.81	1.13	1.85	2.96	4.47	7.45	14.94	21.68
	Case Qty.	50	50	50	30	25	10	10	6	3	2
	UPC 039923-	280848	280855	280862	280879	280886	280893	280909	281029	281036	281043



IRON Y-STRAINER — THREADED END

Fig. No.	Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
T-751-A Class 250 20 Mesh Screen w/Plug	List Price	\$ 17.93	\$ 18.16	\$ 18.16	\$ 26.90	\$ 35.86	\$ 45.95	\$ 63.88	\$ 98.62	\$ 196.20	\$ 270.10
	Unit Wgt.	1.39	1.39	1.39	2.20	3.08	5.06	7.70	12.54	24.42	29.26
	Case Qty.	10	10	10	10	8	6	4	3	1	1
	UPC 039923-	308498	308511	308535	308559	308573	308580	308597	308610	308634	308658



IRON Y-STRAINER — FLANGED

Fig. No.	Size	2"	2 1/2"	3"	4"	5"	6"	8"	10"	12"
F-721-A Class 125 Perforated Screen w/Plug	List Price	\$ 205.10	\$ 223.00	\$ 261.20	\$ 396.70	\$ 722.00	\$ 896.00	\$ 1,586.00	\$ 2,937.00	\$ 4,193.00
	Unit Wgt.	18.04	32.56	37.84	67.10	94.60	136.62	270.60	374.00	605.00
	Case Qty.	1	1	1	1	1	1	1	1	1
	UPC 039923-	308672	308696	308702	308719	308733	308757	308771	308795	308801



IRON Y-STRAINER — FLANGED

Fig. No.	Size	14"	16"
F-721-A Class 125 Perforated Screen w/Plug	List Price	\$ 9,085.00	\$ 12,810.00
	Box Qty	10	10
	Unit Wgt.	863.00	1380.00
	Case Qty.	1	1
	UPC 039923-	310415	310422

BRONZE REPLACEMENT PARTS



20 Mesh Screens

Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
List Price	\$ 16.82	\$ 16.82	\$ 16.82	\$ 16.82	\$ 20.17	\$ 24.66	\$ 28.02	\$ 48.18	\$ 21.29	\$ 42.59
Part Number	T066957PP	T066957PP	T066957PP	T066958PP	T066959PP	T066960PP	T066961PP	T066962PP	T066963PP	T066964PP



Perforated Stainless Steel Screens

Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
List Price	\$ 16.82	\$ 16.82	\$ 16.82	\$ 15.70	\$ 19.39	\$ 19.05	\$ 23.53	\$ 30.26	\$ 42.59	\$ 56.03
Part Number	T066997PP	T066997PP	T066997PP	T066998PP	T066999PP	T067000PP	T067001PP	T067002PP	T067003PP	T067004PP

PTFE Bonnet Gasket

Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
List Price	\$ 0.57	\$ 0.57	\$ 0.57	\$ 0.57	\$ 1.58	\$ 2.02	\$ 2.59	\$ 3.03	\$ 7.17	\$ 12.34
Part Number	T066965PP	T066965PP	T066965PP	T066966PP	T066967PP	T066968PP	T066969PP	T066970PP	T066971PP	T066972PP

NPT Plug

Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
List Price	\$ 1.58	\$ 1.58	\$ 1.58	\$ 1.58	\$ 2.36	\$ 4.83	\$ 4.83	\$ 4.93	\$ 10.88	\$ 17.93
Part Number	T067044PP	T067044PP	T067044PP	T067045PP	T067045PP	E177050FC	E177050FC	E177100FC	E177150FC	E177200FC

IRON REPLACEMENT PARTS



T-751-A — 20 Mesh (1/4" - 2"), 1/16" Perforated (2 1/2" - 3") Stainless Steel Screens

Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
List Price	\$ 2.13	\$ 2.13	\$ 2.13	\$ 2.70	\$ 2.92	\$ 3.37	\$ 3.82	\$ 4.83	\$ 29.14	\$ 39.23
Part Number	RG60009	RG60010	RG60011	RG60012	RG60013	RG60014	RG60015	RG60016	RG60017	RG60018



F-721-A — 1/16" Perforated (2" - 4"), 1/8" Perforated (5" - 16") Stainless Steel Screens

Size	2"	2 1/2"	3"	4"	5"	6"	8"	10"	12"	14"	16"
List Price	\$ 23.53	\$ 30.26	\$ 34.74	\$ 54.91	\$ 108.80	\$ 179.30	\$ 261.20	\$ 378.80	\$ 547.00	\$ 864.00	\$ 1,191.00
Part Number	RG60019	RG60020	RG60021	RG60022	RG60023	RG60024	RG60025	RG60026	RG60027	RG60028	RG60029

T-751-A — Metal-Filled Graphite Bonnet Gasket

Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
List Price	\$ 1.79	\$ 1.79	\$ 1.79	\$ 2.13	\$ 2.36	\$ 2.70	\$ 3.25	\$ 4.38	\$ 5.38	\$ 5.84
Part Number	RG60030	RG60031	RG60032	RG60033	RG60034	RG60035	RG60036	RG60037	RG60038	RG60039

F-721-A — Metal-Filled Graphite Bonnet Gasket

Size	2"	2 1/2"	3"	4"	5"	6"	8"	10"	12"
List Price	\$ 4.49	\$ 5.84	\$ 6.39	\$ 8.63	\$ 11.77	\$ 16.82	\$ 19.05	\$ 21.29	\$ 28.02
Part Number	RG60040	RG60041	RG60042	RG60043	RG60044	RG60045	RG60046	RG60047	RG60048

T-751-A — Iron NPT Plug

Size	1/4"	3/8"	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"
List Price	\$ 3.71	\$ 3.71	\$ 3.71	\$ 3.71	\$ 3.71	\$ 4.49	\$ 4.49	\$ 5.95	\$ 5.95	\$ 8.86
Part Number	RG60001	RG60001	RG60001	RG60002	RG60002	RG60004	RG60004	RG60005	RG60005	RG60006

F-721-A — Iron NPT Plug

Size	2"	2 1/2"	3"	4"	5"	6"	8"	10"	12"
List Price	\$ 3.71	\$ 5.95	\$ 5.95	\$ 10.42	\$ 14.58	\$ 14.58	\$ 14.58	\$ 14.58	\$ 14.58
Part Number	RG60003	RG60005	RG60005	RG60007	RG60008	RG60008	RG60008	RG60008	RG60008

NIBCO[®]
AHEAD OF THE FLOW[®]

NIBCO INC.
WORLD HEADQUARTERS
WEB: www.nibco.com

1516 MIDDLEBURY STREET
ELKHART, IN 46516-4740
USA

DOMESTIC CUSTOMER SERVICE
PHONE: 800.234.0227
FAX: 800.234.0557

TECHNICAL SERVICE
PHONE: 888.446.4226
FAX: 888.336.4226

INTERNATIONAL OFFICE
PHONE: +1/574.295.3327
FAX: +1/574.295.3455