


# Stop & Waste Valves

125 lb. CWP to 100 ° F


Maximum Temperature 180 ° F

CSA B125 Approved and IAPMO Listed



## 75-CLT


DESCRIPTION	*NOM. SIZE	DIMENSIONS		APPROX. NET WT.
		A	B	
Stop & Waste Valve Female Thread	1/2"	2 <sup>3</sup> / <sub>16</sub> "	2 <sup>9</sup> / <sub>16</sub> "	.50 lb



## 4476±


DESCRIPTION	NOM. SIZE	DIMENSIONS		APPROX. NET WT.
		B	C	
Stop & Waste Valve Comp. x Comp.	1/2"	2 <sup>9</sup> / <sub>16</sub> "	1 <sup>5</sup> / <sub>8</sub> "	.60 lb
	3/4"	2 <sup>9</sup> / <sub>16</sub> "	1 <sup>11</sup> / <sub>16</sub> "	.80 lb

± - Not CSA or IAPMO Listed




## 4776±

DESCRIPTION	NOM. SIZE	DIMENSIONS		APPROX. NET WT.
		B	C	
Stop & Waste Valve CPVC x CPVC	1/2"	2 <sup>9</sup> / <sub>16</sub> "	3"	.62 lb
	3/4"	2 <sup>9</sup> / <sub>16</sub> "	3 <sup>1</sup> / <sub>16</sub> "	.74 lb




## 77

DESCRIPTION	NOM. SIZE	DIMENSIONS			APPROX. NET WT.
		B	H	J	
Angle Stop Valve Female	1/2"	2 <sup>9</sup> / <sub>16</sub> "	1 <sup>1</sup> / <sub>16</sub> "	1 <sup>5</sup> / <sub>16</sub> "	.50 lb
	3/4"	2 <sup>11</sup> / <sub>16</sub> "	1 <sup>3</sup> / <sub>16</sub> "	1"	.60 lb



## 777

DESCRIPTION	NOM. SIZE	DIMENSIONS			APPROX. NET WT.
		B	F	G	
Stop & Waste Valve CPVC x CPVC	1/2"	2 <sup>7</sup> / <sub>16</sub> "	1/2"	3/8"	.40 lb
	3/4"	2 <sup>9</sup> / <sub>16</sub> "	5/8"	7/16"	.50 lb



## 777-17

DESCRIPTION	NOM. SIZE	DIMENSIONS			APPROX. NET WT.
		B	G	H	
Angle Stop Valve Cup to Female	3/4"	2 <sup>7</sup> / <sub>16</sub> "	7/16"	1 <sup>7</sup> / <sub>16</sub> "	.60 lb