


Stop & Stop Waste Valves - Straight

125 lb. CWP to 100 ° F


Maximum Temperature 180 ° F



75-CL

DESCRIPTION	NOM. SIZE	DIMENSIONS		APPROX. NET WT.
		A	B	
Stop Valve FIP x FIP	1/2"	2 ³ / ₁₆ "	2 ⁹ / ₁₆ "	.50 lb
	3/4"	2 ⁵ / ₁₆ "	2 ⁹ / ₁₆ "	.60 lb


IAPMO Listed to cUPC®



725-CL

DESCRIPTION	NOM. SIZE	DIMENSIONS		APPROX. NET WT.
		B	C	
Stop Valve Cup x Cup	1/2"	2 ⁹ / ₁₆ "	1 ³ / ₁₆ "	.40 lb
	3/4"	2 ⁹ / ₁₆ "	1 ³ / ₁₆ "	.50 lb


IAPMO Listed to cUPC®



76-CL

DESCRIPTION	NOM. SIZE	DIMENSIONS		APPROX. NET WT.
		A	B	
Stop & Waste Valve FIP x FIP	1/2"	2 ³ / ₁₆ "	2 ⁹ / ₁₆ "	.54 lb
	3/4"	2 ⁵ / ₁₆ "	2 ⁹ / ₁₆ "	.60 lb

IAPMO Listed to cUPC®




726-CL, 726-LCL

DESCRIPTION	NOM. SIZE	DIMENSIONS		APPROX. NET WT.
		B	C	
Stop & Waste Valve Cup x Cup	1/2"	2 ⁹ / ₁₆ "	1 ³ / ₁₆ "	.42 lb
	3/4" ‡	2 ⁹ / ₁₆ "	1 ³ / ₁₆ "	.49 lb

IAPMO Listed to cUPC®


‡ - Not CSA Listed



4476

DESCRIPTION	NOM. SIZE	DIMENSIONS		APPROX. NET WT.
		B	C	
Stop & Waste Valve Comp. x Comp.	1/2"	2 ⁹ / ₁₆ "	1 ⁵ / ₈ "	.60 lb
	3/4" ‡	2 ⁹ / ₁₆ "	1 ¹¹ / ₁₆ "	.80 lb

‡ - Not CSA Listed



4776


DESCRIPTION	NOM. SIZE	DIMENSIONS		APPROX. NET WT.
		B	C	
Stop & Waste Valve CPVC x CPVC	1/2"	2 ⁹ / ₁₆ "	3"	.62 lb
	3/4" ‡	2 ⁹ / ₁₆ "	3 ¹ / ₁₆ "	.74 lb

‡ - Not CSA Listed

Stop Valves - Angle

125 lb. CWP to 100 ° F


Maximum Temperature 180 ° F



77

DESCRIPTION	NOM. SIZE	DIMENSIONS			APPROX. NET WT.
		B	H	J	
Angle Stop Valve Female	1/2"	2 ⁹ / ₁₆ "	1 ¹ / ₁₆ "	1 ⁵ / ₁₆ "	.50 lb
	3/4"	2 ¹¹ / ₁₆ "	1 ³ / ₁₆ "	1"	.60 lb


IAPMO Listed to cUPC®



777

DESCRIPTION	NOM. SIZE	DIMENSIONS			APPROX. NET WT.
		B	F	G	
Stop & Waste Valve CPVC x CPVC	1/2"	2 ⁷ / ₁₆ "	1/2"	3/8"	.40 lb
	3/4"	2 ⁹ / ₁₆ "	5/8"	7/16"	.50 lb

IAPMO Listed to cUPC®



777-17

DESCRIPTION	NOM. SIZE	DIMENSIONS			APPROX. NET WT.
		B	G	H	
Angle Stop Valve Cup to Female	3/4"	2 ⁷ / ₁₆ "	7/16"	1 ⁷ / ₁₆ "	.60 lb